

E11019




Wiring block

ZDO6H05DMSS0005H15

Article no longer available - archive entry

Alternative articles: EBC020

When selecting an alternative article and accessories please note that technical data may differ!



Application

System	Free from silicone; Halogen-free; gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	10...30 DC
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12

Outputs

Electrical design	PNP
-------------------	-----

Operating conditions

Ambient temperature	[°C]	-15...80
---------------------	------	----------

E11019



Wiring block

ZDO6H05DMSS0005H15

Protection	IP 67
------------	-------

Mechanical data

Material	TPU (urethane)
Molded-body material	TPU (urethane)
Number of ports splitter box	6
Connector type	M12

Displays / operating elements

Display	Switching status	12 x LED, yellow
	Power	1 x LED, green

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 10.4 mm; 12 x 0.5 mm² (63 x Ø 0.1 mm) + 3 x 1.0 mm² (127 x Ø 0.1 mm)

Electrical connection - slot

Connector: 6 x M12; coding: A; Moulded body: TPU (urethane); Contacts: gold-plated; Tightening torque: 0.5 Nm




E11019



Wiring block

ZDO6H05DMSS0005H15

Connection



BN =	Core colors :
BU =	brown
GN =	blue
GY =	green
PK =	grey
RD =	pink
WH =	red
YE =	white
	yellow