


E11020



Wiring block

ZDO6H05DMSS0010H15

Article no longer available - archive entry




Application		
System		Free from silicone; Halogen-free; gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	10...30 DC
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-15...80
Protection		IP 67

E11020



Wiring block

ZDO6H05DMSS0010H15

Mechanical data		
Material	TPU (urethane)	
Molded-body material	TPU (urethane)	
Number of ports splitter box	6	
Connector type	M12	
Displays / operating elements		
Display	Switching status	12 x LED, yellow
	Power	1 x LED, green
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 10 m, PUR, Halogen-free; 12 x 0.5 mm ² (63 x Ø 0.1 mm) + 3 x 1.0 mm ² (127 x Ø 0.1 mm)		
Electrical connection - slot		
Connector: 6 x M12; coding: A; Moulded body: TPU (urethane); Contacts: gold-plated; Tightening torque: 0.5 Nm		
		


E11020



Wiring block

ZDO6H05DMSS0010H15

Connection



BN =	Core colors :
BU =	brown
GN =	blue
GY =	green
PK =	grey
RD =	pink
WH =	red
YE =	white
	yellow