


E12736




Connecting cordset with AMP connector

ecomatPanel/Cable/5m



Application		
System		screened cable
Electrical data		
Operating voltage	[V]	8...32 DC
Protection class		III
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-40...80
Protection		IP 20; (without resistor)
Mechanical data		
Weight	[g]	456.4
Dimensions	[mm]	89.5 x 33.4 x 47.3
Material		housing: PBT-GF20
Molded-body material		PBT
Remarks		
Pack quantity		1 pcs.

Electrical connection	
Cable: 5 m, PUR, grey, Ø 8.3 mm, screened; 2 x 0.5 mm² (twisted pairs) + 2 x 0.5 mm² (twisted pairs)	
Connector: AMP MQS, straight; Moulded body: PBT; Contacts: tin-plated	




E12736



Connecting cordset with AMP connector

ecomatPanel/Cable/5m

Connection



1	CAN_L
2	CAN_H
3	GND
4	Vbb