


E18162



Wirable plug

SSTGH040VASFPKG9



Application

Application	Industrial applications
-------------	-------------------------

Electrical data

Operating voltage	[V]	< 250 AC / < 300 DC
Max. current load total	[A]	4

Operating conditions

Ambient temperature	[°C]	-40...85
Protection		IP 68

Mechanical data

Weight	[g]	27.216
Dimensions	[mm]	20 x 20 x 52
Molded-body material		PA
Material nut		stainless steel (1.4571/316Ti)

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: ...0.75 mm²; Cable sheath: Ø 6...8 mm

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Contacts: 4, pre-coppered brass; Moulded body: PA; Locking: stainless steel (1.4571/316Ti)



Connection

