AC2514


AS-Interface ClassicLine module

ClassicL45 2DO-y 2DI-y T M12

Article no longer available - archive entry

Alternative articles: AC5214

When selecting an alternative article and accessories please note that technical data may differ!



1 panel for labelling
2 fixture infrared adapter

Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	150
Max. current load total	[A]	2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	18...30; (via flat cable)
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	6...10
Input current low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

AC2514

AS-Interface ClassicLine module

ClassicL45 2DO-y 2DI-y T M12

Outputs						
Electrical design		AS-i				
Number of digital outputs		2				
Circuit		PNP				
Voltage range DC	[V]	15...30; (to PELV; via flat cable)				
Max. current load per output	[mA]	1000; (utilization category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))				
Short-circuit proof		yes				
Electrically separated		yes				
Operating conditions						
Ambient temperature	[°C]	-25...70				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
AS-i classification						
AS-i version		2.1				
AS-i addressing		IR addressing possible				
Extended addressing mode		yes				
AS-i profile		S-B.A.E				
AS-i I/O configuration	[hex]	B				
AS-i ID code	[hex]	A.E				
Data bits		Data bit	D0	D1	D2	D3
		Input	-	-	3	4
		Socket	-	-	I-3/4	I-3/4 I-4
		Pin	-	-	4	2 4
		Output	1	2	-	-
		Socket	O-1/2	O-1/2 / O-2	-	-
		Pin	4	2 4	-	-
Mechanical data						
Weight	[g]	114.4				
Type of mounting		AS-i interface to FC-E lower parts				
Material		PBT				
Displays / operating elements						
Display		Power	LED, green			
		errors	LED, red			
		Function	LED, yellow			
Accessories						
Accessories (optional)		Module lower part				
Remarks						
Remarks		Inputs and outputs must be electrically isolated.				
		Do not connect any of the following points to an external potential:				
		I-, I+, I-3/4, I-4				
		The connections are electrically connected with the AS-i cable.				
Pack quantity		1 pcs.				

AC2514


AS-Interface ClassicLine module

ClassicL45 2DO-y 2DI-y T M12

Electrical connection

contact pins to module lower part, FK-E:

Connection



Connector: M12

	Inputs
	Socket I-3/4
1	voltage supply L+
2	Data input 4
3	Sensor supply L-
4	Data input 3
5	not used
	Socket I-4
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 4
5	not used
	Outputs
	Socket O-1/2
1	not used
2	Switching output 2
3	External voltage AUX -
4	Switching output 1
5	not used
	Socket O-2
1	not used
2	not used
3	External voltage AUX -
4	Switching output 2
5	not used