




Fiber optic diffuse reflection sensor

FT-00-M-V-E3/1,5M



Application		
Function principle	Diffuse reflection sensor	
Application	High temperature resistance; Robust design for use in harsh industrial environments; Resistant to various aggressive chemicals	
Monitoring range		
Range with fiber optic amplifier type	OCF; OKF; OOF; OUF	
OCF (High Power)		
Range fiber optics	[mm]	350
OKF		
Range fiber optics	[mm]	36
OOF		
Range fiber optics	[mm]	180
OUF		
Range fiber optics	[mm]	36
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Weight	[g]	108.5
Version of sensing head	straight	
Sensing head diameter	[mm]	3

E20526



Fiber optic diffuse reflection sensor

FT-00-M-V-E3/1,5M

Sensing head length	[mm]	10
Total length	[mm]	1500
Min. bending radius	[mm]	20
Fiber arrangement		⓪
Fiber material		glass
Fiber head material		stainless steel (1.4305 / 303)
Fiber sheath material		metal silicone

Accessories

Items supplied	E20102
----------------	--------

Remarks

Pack quantity	1 pcs.
---------------	--------