


AC2637



I/O module for field applications

FieldModuleDP 4AO (C) M12

Article to be discontinued



Electrical data

Operating voltage	[V]	20...29 DC
Current consumption	[mA]	< 115
Electrical separation		no

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 4
------------------------------	-----------------------------

Outputs

Number of analog outputs	4
--------------------------	---

AC2637



I/O module for field applications

FieldModuleDP 4AO (C) M12

Analog current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit proof		yes
Actuator supply outputs		from load voltage

Accuracy / deviations

Measuring error		< ± 0,3
	[% of the final value]	

Interfaces

PROFIBUS

Transmission rate	9,6...12000 kBit/s
-------------------	--------------------

Operating conditions

Ambient temperature	[°C]	0...55
Storage temperature	[°C]	-25...85
Protection		IP 67

Tests / approvals

EMC	EN 50081-2	
	EN 50082-2	
Vibration resistance	IEC 68	parts 2-6 / IEC 68, parts 2-27

Mechanical data


Weight	[g]	300.5
Material	housing: PA 6; potting compound: PU; contact pins: brass gold-plated	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - PROFIBUS

Connector: M12; coding: B



	plug M12 PROFIBUS In
1	not used
2	line A
3	GND
4	line B
5	screen
	Socket M12 PROFIBUS Out
1	5 V DC
2	line A
3	GND
4	line B
5	screen

AC2637



I/O module for field applications


FieldModuleDP 4AO (C) M12

Electrical connection - Process connection

Connector: M12; coding: A



Connection



	Socket M12 Outputs
1	Output +
2	24 V DC UL
3	Output GND
4	GND
5	screen

Electrical connection - voltage supply

Connector: M8; coding: A



	plug M8
1	24 V DC UB
2	24 V DC UL
3	GND
4	GND
	Socket M8
1	24 V DC UB
2	24 V DC UL
3	GND
4	GND