


# E20715



## Fiber optic diffuse reflection sensor

FT-11-E-V-E6R/2m



Application	
Function principle	Diffuse reflection sensor
Application	For use in industrial environments
Monitoring range	
Range with fiber optic amplifier type	OB50; OBF; OCF; OO50
OB50	
Range fiber optics [mm]	40
OBF	
Range fiber optics [mm]	60
OCF (High Power)	
Range fiber optics [mm]	420
OO50	
Range fiber optics [mm]	150
Operating conditions	
Ambient temperature [°C]	-40...70
Mechanical data	
Weight [g]	52
Version of sensing head	angled
Sensing head diameter [mm]	6

# E20715



## Fiber optic diffuse reflection sensor

FT-11-E-V-E6R/2m

Total length	[mm]	2000
Min. bending radius	[mm]	25
Fiber arrangement		⊙
Fiber material		PMMA
Fiber head material		stainless steel (1.4305 / 303)
Fiber sheath material		PE
<b>Accessories</b>		
Items supplied		E20103
<b>Remarks</b>		
Pack quantity		1 pcs.