




Sensing head for fiber optic diffuse reflection sensor

FT-11-EPA-M8x40/F2x1



Application		
Function principle		Diffuse reflection sensor
Monitoring range		
Range with fiber optic amplifier type		OB50; OBF; OO50
OB50		
Range fiber optics	[mm]	55
OBF		
Range fiber optics	[mm]	110
OO50		
Range fiber optics	[mm]	235
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	16.2
Version of sensing head		straight
Sensing head thread		M8
Total length	[mm]	configurable
Fiber arrangement		⊙⊙
Core diameter	[mm]	2 x 1.5

E20765



Sensing head for fiber optic diffuse reflection sensor

FT-11-EPA-M8x40/F2x1

Material	housing: brass white bronze coated
Fiber material	PMMA
Fiber head material	aluminum
Accessories	
Items supplied	Hexagon nuts: 2 x M8
	washers: 2
Remarks	
Pack quantity	1 pcs.