

# AC2723




## AS-Interface module for valve heads

ValveheadModule 2DI/2DO T ST

Article no longer available - archive entry

Alternative articles: AC2731

When selecting an alternative article and accessories please note that technical data may differ!



### Electrical data

Operating voltage	[V]	26.5..31.6 DC
Current consumption	[mA]	250
Integrated watchdog		yes

### Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 2
------------------------------	---

### Inputs

Number of digital inputs	2
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply	[V] 18...30
Max. total current rating of inputs	[mA] 100
Input current High	[mA] 6...10
Input current low	[mA] 0...2
Switching level high	[V] > 10
Digital inputs protected against short circuits	yes

### Outputs

Electrical design	PNP
-------------------	-----

# AC2723



## AS-Interface module for valve heads

ValveheadModule 2DI/2DO T ST

Number of digital outputs	2
Max. current load per output [mA]	50
Short-circuit proof	yes
<b>Operating conditions</b>	
Ambient temperature [°C]	-25...85
Protection	IP 00
<b>Tests / approvals</b>	
EMC	EN 50295
<b>AS-i classification</b>	
AS-i profile	S-3.0
AS-i I/O configuration [hex]	3
AS-i ID code [hex]	0
<b>Displays / operating elements</b>	
Display	Power LED, green Function LED, yellow
<b>Remarks</b>	
Remarks	The AS-i valve top module contains an AS-i slave as well as two digital inputs and two digital outputs. The supply of the pcb and all peripherals is carried out via AS-Interface. The module has been designed especially for the use in valve tops. Two inductive sensors detect the open/closed position and one or two solenoid valves are used for pneumatic triggering. The printed conductors are coated with a protecting lacquer against corrosion. The integrated watchdog ensures that the solenoids are switched off in case of a bus communication failure.
Pack quantity	1 pcs.

# AC2723




## AS-Interface module for valve heads

ValveheadModule 2DI/2DO T ST

### Electrical connection

screw terminals:

### Connection



A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
I1/I2	Switching input sensor 1...2
O3/O4	Switching output actuator 1...2