




Fiber optic diffuse reflection sensor

FT-30-A-A-R8

Article no longer available - archive entry



Application		
Function principle	Diffuse reflection sensor	
Application	High temperature resistance; Robust design for use in harsh industrial environments	
Monitoring range		
Range with fiber optic amplifier type	OIF	
OIF		
Range fiber optics	[mm]	70
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Weight	[g]	93.8
Version of sensing head	angled	
Sensing head diameter	[mm]	8
Total length	[mm]	600
Min. bending radius	[mm]	30; (for fixed installation)
Fiber arrangement		
Material	Adapter: PA	
Fiber material	glass	

E20153



Fiber optic diffuse reflection sensor

FT-30-A-A-R8

Fiber head material	aluminum
Fiber sheath material	aluminum
Accessories	
Items supplied	E20353
Remarks	
Pack quantity	1 pcs.