




Fiber optic diffuse reflection sensor

FT-11-M-V-M6/2M

Article no longer available - archive entry



Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Monitoring range

Range with fiber optic amplifier type	OB5030
---------------------------------------	--------

OB50

Range fiber optics [mm]	32
-------------------------	----

Operating conditions

Ambient temperature [°C]	-20...150
--------------------------	-----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	2000
Min. bending radius [mm]	20
Fiber material	glass
Fiber head material	stainless steel (1.4305 / 303)
Fiber sheath material	metal silicone

Remarks

Pack quantity	1 pcs.
---------------	--------