


E2M250



MultiViewBox

MULTIVIEWBOX/4 PORT



- 1 INPUT
- 2 OUTPUT
- 3 C4
- 4 C3
- 5 C2
- 6 C1



Product characteristics

Image resolution [px] 680 x 480

Electrical data

Operating voltage [V] 10...32 DC

Current consumption [mA] < 770

Overvoltage protection yes

Monitoring range

Image resolution [px] 680 x 480

Operating conditions

Ambient temperature [°C] -40...85

E2M250



MultiViewBox

MULTIVIEWBOX/4 PORT

Storage temperature	[°C]	-40...125
Storage humidity	[%]	< 75; (relative humidity)
Shelf life	[MON]	24
Protection		IP 67; (ISO 20653)

Tests / approvals

EMC	DIN EN 61000-6-4	industrial environments
	DIN EN 61000-6-2	industrial environments
Shock resistance		50 g
Vibration resistance	Frequency range 24...2000 Hz	
	(15.3 x 9.81 m/s ²)rms	PSD (g ² /Hz)
	0.04...0.1	

Mechanical data

Weight	[g]	1569.5
Material		housing: stainless steel (1.4401 / 316)

Accessories

Items supplied	Protective covers
----------------	-------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - ..C4

Connector: 4 x M16; coding: A



1	coax cable core video signal
2	coax screen video GND
3	U+
4	0 V

E2M250




MultiViewBox

MULTIVIEWBOX/4 PORT

Electrical connection - INPUT


Connector: 1 x M16; coding: A



1	U+
2	0 V
3	Input 1
4	Input 2
5	Input 3
6	Input 4
7	not used
8	not used

Electrical connection - OUTPUT

Connector: 1 x M16; coding: A



1	coax cable core video signal
2	coax screen video GND
3	not used
4	not used