



E2M251



Connection cable for E2M250 multi-view box

CONNECTION CABLE M16 8P 3,85M



Application		
System	Halogen-free; Drag chain suitability	
Design	For connection of the MultiViewBox E2M250	
Electrical data		
Operating voltage	[V]	< 60 DC
Operating conditions		
Ambient temperature	[°C]	-45...85
Protection		IP 67
Mechanical data		
Weight	[g]	322.8
Material	housing: diecast zinc; sealing: PBT	
Material nut	diecast zinc	
Drag chain suitability	yes	
Drag chain suitability	Bending radius for fixed installation	≥ 100 mm
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 3.85 m, PUR, Halogen-free, black, Ø 6 mm; 7 x 0.34 mm²		
Electrical connection - Socket		
Connector: 1 x M16, straight; coding: A; Locking: diecast zinc		
		
1	12 / 24 V DC red	
2	GND white	
3	IN 1 blue	
4	IN 2 brown	
5	IN 3 white/yellow	
6	IN 4 grey	
7	not used	
8	not used	