


AC2916



AS-Interface ProcessLine module

ProcessLine 4AI C IP69K



Application

Application

sanitary and wet areas in the food industry

Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	450
Reverse polarity protection		yes

Inputs / outputs

Number of inputs and outputs

Number of analog inputs: 4

Inputs

Sensor supply of the inputs		AS-i
Number of analog inputs		4; (connection of 2- and 3-wire sensors)
Analog input (current)	[mA]	4...20
Analog input (voltage)	[V]	18...30
Max. voltage drop across load for nominal voltage	[V]	10
Resolution of analog input		1 bit = 1 μ A
Precision analog input	[%]	0,5

Operating conditions

Ambient temperature	[°C]	-5...70
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90; (linearly decreasing to 50 % (40 °C) non condensing)
Max. height above sea level	[m]	2000
Protection		IP 68; IP 69K
Degree of soiling		2

Tests / approvals

EMC	EN 62026-2
	EN 61000-6-2



AS-Interface ProcessLine module

ProcessLine 4AI C IP69K

MTTF	[years]	98
------	---------	----

AS-i classification

AS-i version		2.11; 3.0
Extended addressing mode		no
AS-i master profile		M3; M4
AS-i profile		S-7.3.E
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	3.E
AS-i certificate		101108

Mechanical data

Weight	[g]	607
Dimensions	[mm]	Ø 137.3 / L = 80
Material		threaded bush: stainless steel (1.4404 / 316L); LED-Fenster: PC; O-ring: EPDM; Protective cap: PP

Displays / operating elements

Display	analog signal	LED, yellow Channels AI1...AI4
	Power	LED, green AS-i
	errors	LED, red

Electrical connection

Module connection	M12
-------------------	-----

Accessories


Accessories (optional)	Protective cap: M12, E70297
	Flat cable insulation displacement connector:, E70455
	Torque wrench:, E70390

Remarks

Remarks	When the sensors and actuators are supplied from AS-i the load must not exceed a maximum of 380 mA.
	The load for an individual sensor connection must not exceed 200 mA.
	There is an electrical connection between the sensor and AS-i.
	MEW = % of the final value of the measuring range
Pack quantity	1 pcs.

Electrical connection - AS-i

Connector: 1 x M12; coding: A; Tightening torque: 1.2...1.4 Nm



- | | |
|----|-----------------------|
| 1: | AS-i + |
| 2: | n.c. |
| 3: | AS-i - |
| 4: | n.c. |
| 5: | functional earth (FE) |

AC2916




AS-Interface ProcessLine module

ProcessLine 4AI C IP69K

Electrical connection - Process connection

Connector: 4 x M12; coding: A; Tightening torque: 1.2...1.4 Nm



Inputs	
1	Sensor supply + 24 V
2	AI+
3	Sensor supply 0 V / AI-
4	n.c.
5	functional earth (FE)