

AC2026




AS-Interface illuminated pushbutton module

EMS Module 2BI 2LO

Article no longer available - archive entry

Alternative articles: AC2086
When selecting an alternative article and accessories please note that technical data may differ!



- 1 panel for labelling
- 2 pushbutton / LED
- 3 pushbutton / LED



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	55
Inputs		
Sensor supply of the inputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67
Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i version		2.1
Extended addressing mode		no
AS-i master profile		M2; M3; M4



AS-Interface illuminated pushbutton module

EMS Module 2BI 2LO

AS-i profile	S-3.F.F				
AS-i I/O configuration [hex]	3				
AS-i ID code [hex]	F.F				
AS-i certificate	04801				
Data bits	Data bit	D0	D1	D2	D3
	pushbutton	2	1	-	-
	LED	-	-	2	1

Mechanical data

Weight [g]	100.6
Type of mounting	AS-i interface to FC and SC lower parts
Material	PBT

Displays / operating elements

Display	pushbuttons	2 x LED, white
---------	-------------	----------------

Accessories

Items supplied	cover support: 2				
	color inserts: 2, red				
	2, green				
	2, yellow				
	2, blue				
	2, white				

Remarks

Remarks	The pushbuttons (EAO type 84) provide protection against accidental contact.				
	Housing and pushbuttons can be labeled.				
Pack quantity	1 pcs.				

Electrical connection

contact pins to module lower part, FK / PG:					
---	--	--	--	--	--