


# E43212



## Coaxial tube for level sensors

LR COAX TUBE G3/4 L450



1 Fixing bracket for centring piece

### CRN

Application	
Design	for level sensors LR
Medium temperature [°C]	-40...200
Pressure rating	16 bar   1.6 MPa
Vacuum resistance	-1000 mbar   -0.1 MPa
MAWP (for applications according to CRN) [bar]	16
Mechanical data	
Weight [g]	290.5
Material	Coaxial tubes for level sensors: stainless steel (1.4301 / 304); sealing: NBR fiber-reinforced; centring piece: PPS fiber-reinforced; fixing bracket: stainless steel (1.4310 / 301)
Sensor connection	threaded connection G 3/4 Internal thread
Process connection	threaded connection G 3/4 external thread
Length L [mm]	450
Accessories	
Items supplied	sealing: 1
Remarks	
Pack quantity	1 pcs.