


E43214



Coaxial tube for level sensors

LR COAX TUBE G3/4 L1000



1 fixing bracket for centering piece

CRN

| Application | |
|--|--|
| Design | for level sensors LR |
| Medium temperature [°C] | -40...200 |
| Pressure rating | 16 bar 1.6 MPa |
| Vacuum resistance | -1000 mbar -0.1 MPa |
| MAWP (for applications according to CRN) [bar] | 16 |
| Mechanical data | |
| Weight [g] | 570 |
| Material | Coaxial tubes for level sensors: stainless steel (1.4301 / 304); sealing: NBR fiber-reinforced; centring piece: PPS fiber-reinforced; fixing bracket: stainless steel (1.4310 / 301) |
| Sensor connection | threaded connection G 3/4 Internal thread |
| Process connection | threaded connection G 3/4 external thread |
| Length L [mm] | 1000 |
| Accessories | |
| Items supplied | sealing: 1 |
| Accessories (optional) | Centering piece for coaxial tubes: 1, E43222 |
| Remarks | |
| Remarks | When used under DNV GL conditions mounting of an additional centring piece is required |
| Pack quantity | 1 pcs. |