




AS-Interface illuminated pushbutton module

EMS-Module 2BI 2LO RD/GN

Article no longer available - archive entry



- 1 panel for labelling
- 2 LED
- 3 pushbutton / LED
- 4 key-operated switch



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	55
Inputs		
Sensor supply of the inputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...85
Protection		IP 40; (with protective cover: IP 54)
Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i version		2.1
Extended addressing mode		yes
AS-i master profile		M2; M3; M4
AS-i profile		S-B.A.E
AS-i I/O configuration	[hex]	B
AS-i ID code	[hex]	A.E

AC2087



AS-Interface illuminated pushbutton module

EMS-Module 2BI 2LO RD/GN

AS-i certificate	49202				
Data bits	Data bit	D0	D1	D2	D3
	assignment	not used	LED	key-operated switch	pushbutton

Mechanical data	
Weight	[g] 117.5
Type of mounting	AS-i interface to FC and SC lower parts
Material	PBT

Displays / operating elements	
Display	Power
	LED, green
	errors
	LED, red

Remarks	
Remarks	The pushbuttons (EAO type 84) provide protection against accidental contact.
	Housing and pushbuttons can be labeled.
Pack quantity	1 pcs.

Electrical connection	
contact pins to module lower part, FK / PG:	