


# E43230



## Coaxial tube for level sensors

LR COAX TUBE G3/4 L150



1 Gasket

### CRN

Application		
Design		for level sensors LR
Medium temperature	[°C]	-20...200
Pressure rating	[bar]	16
Vacuum resistance	[mbar]	-1000
MAWP (for applications according to CRN)	[bar]	16
Mechanical data		
Weight	[g]	135
Material		Coaxial tubes for level sensors: stainless steel (1.4301 / 304); sealing: NBR fiber-reinforced; centring piece: PPS fiber-reinforced; Fixing strap: stainless steel (1.4310 / 301)
Sensor connection		threaded connection G 3/4 Internal thread
Process connection		threaded connection G 3/4 external thread
Length L	[mm]	150
Accessories		
Items supplied		sealings: 1
Remarks		
Pack quantity		1 pcs.