


E70202



Connection cable

VDOAH030VAS0001E03STGH030VAS

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Operating conditions		
Ambient temperature	[°C]	-25...100
Protection		IP 67
Mechanical data		
Dimensions	[mm]	15 x 15 x 41.5
Material		PVC
Molded-body material		PVC
Material nut		stainless steel (1.4404 / 316L)
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L)



E70202




Connection cable

VDOAH030VAS0001E03STGH030VAS

Electrical connection

Cable: 1 m, PVC; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L)

