


E80415



RFID tag

ID-TAG/10,1X3,9/03 (10 pieces)



mounting hole: Ø 10.0 x 3.7 mm



Application

Operating temperature (active)	[°C]	-40...85
Peak temperature (passive)	[°C]	90

Electrical data

Operating frequency	[MHz]	13,56
Memory size	[bit]	896
Memory type		EEPROM
Chip type		ICODE SLIX
Number of the blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693
Max. read cycles		unlimited
Max. write cycles		100000

Operating conditions

Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...90
Protection		IP 68

Tests / approvals

Radio approval	ISO 15693
----------------	-----------

Mechanical data

Weight	[g]	5.4
Type of mounting		Press-fit housing; Installation in metal
Dimensions	[mm]	Ø 10.3 / L = 4
Material		housing: PPA GF30; epoxy resin

Remarks

Pack quantity	10 pcs.
---------------	---------