

AC5012




Lower part for AS-Interface module

EMS-Base FC Addr.-socket V2A

Article no longer available - archive entry

Alternative articles: AC5014

When selecting an alternative article and accessories please note that technical data may differ!



- 1 contact pins
- 2 panel for labelling
- 3 Addressing socket



Electrical data

Operating voltage [V] 26.5...31.6 DC

Outputs

Electrical design AS-i
Contact rating < 2 A

Operating conditions

Ambient temperature [°C] -25...85
Protection IP 67; (depending on the upper part used: IP 20 / IP 65 / IP 67)

AS-i classification

AS-i addressing Addressing socket

Mechanical data

Type of mounting Mounting on DIN rail and panel
Dimensions [mm] 45 x 80 x 20
Material PBT; stainless steel (1.4305 / 303)

Remarks

Pack quantity 1 pcs.

AC5012



Lower part for AS-Interface module

EMS-Base FC Addr.-socket V2A

Electrical connection

contact pins in module upper part :

quick mounting technology for AS-i flat cable: