



AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y 2A IP67



Application		
Application	field installation	
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; (cULus - Class 2 source required)
Max. current consumption from AS-i	[mA]	150
Max. current load total	[A]	4
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 2	
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	18...30; (via flat cable)
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	6...10
Input current low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes



AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y 2A IP67

Outputs						
Number of digital outputs		2				
Circuit		PNP				
Voltage range DC [V]		15...30; (to PELV; via flat cable)				
Max. current load per output [mA]		2000; (utilization category DC-13 (control of electromagnets): 40 W (IEC 60947-5-1))				
Short-circuit proof		yes				
Electrically separated		yes				
Actuator supply outputs		AUX				
Operating conditions						
Ambient temperature [°C]		-25...70				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
		IEC 61000-6-2				
AS-i classification						
AS-i version		2.11; 3.0				
AS-i addressing		Addressing socket				
Extended addressing mode		yes				
AS-i master profile		M2; M3; M4				
AS-i profile		S-B.A.E				
AS-i I/O configuration [hex]		B				
AS-i ID code [hex]		A.E				
Data bits		Data bit	D0	D1	D2	D3
		Input	-	-	3	4
		Socket	-	-	I-3/4	I-3/4 I-4
		Pin	-	-	4	2 4
		Output	1	2	-	-
		Socket	O-1/2	O-1/2 / O-2	-	-
		Pin	4	2 4	-	-
Mechanical data						
Weight [g]		187.5				
Type of mounting		AS-i flat cable connection				
Material		PA; Piercing contacts: CuSn6 nickel-plated and tin-plated				
Displays / operating elements						
Display		Power		LED, green		
		errors		LED, red		
		Function		LED, yellow		
Electrical connection						
Module connection		Flat cable				
Accessories						
Items supplied		lower part				
Accessories (optional)		Protective cap: M12, E73004				




AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y 2A IP67

Remarks	
Remarks	Inputs and outputs must be electrically isolated.
	Do not connect any of the following points to an external potential:
	L-, L+, I-3/4, I-4
	The connections are electrically connected with the AS-i cable.
Pack quantity	1 pcs.

Electrical connection
quick mounting technology for AS-i flat cable: ; three selectable directions

Electrical connection - Inputs
Connection



Connector: M12	
	Inputs
	Socket I-3/4
1	Sensor supply L+
2	Data input 4
3	Sensor supply L-
4	Data input 3
5	not used
	Socket I-4
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 4
5	not used




AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y 2A IP67

Electrical connection - Outputs

Connection



Connector: M12

Outputs	
Socket O-1/2	
1	not used
2	Switching output 2
3	External voltage AUX -
4	Switching output 1
5	not used
Socket O-2	
1	not used
2	not used
3	External voltage AUX -
4	Switching output 2
5	not used