


AL2605



IO-Link input/output module

IOL MOD PL 8XMP/DX E M12 IP67



Depending on the version some LEDs are inactive



Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	100; (US)
Protection class		III
Additional voltage supply	[V]	18...30 DC; (UA UAi)
Max. current consumption from additional supply	[mA]	16000; (UA; UAi: 800 mA)
Inputs / outputs		
Total number of inputs and outputs		16



IO-Link input/output module

IOL MOD PL 8XMP/DX E M12 IP67

Number of inputs and outputs		Number of digital inputs: 16; Number of analog inputs: 8; Number of digital outputs: 16	
Inputs			
Number of digital inputs		16; (configurable)	
Input circuit of digital inputs		PNP; (type 3 (IEC 61131-2))	
Sensor supply of the inputs		AUX (UA, UAi)	
Voltage supply	[V]	18...30	
Input current High	[mA]	2...15	
Input current low	[mA]	0...1.5	
Switching level high	[V]	11...28	
Switching level low	[V]	0...5	
Number of analog inputs		8; (configurable current/voltage input)	
Analog input (current)	[mA]	4...20	
Analog input (voltage)	[V]	0...10	
Resolution of analog input		16 Bit	
Outputs			
Number of digital outputs		16; (configurable)	
Max. current load per output	[mA]	2000	
Max. current load outputs total	[A]	16	
Short-circuit protection		yes	
Actuator supply outputs		AUX (UA)	
Interfaces			
Communication interface		IO-Link	
SDCI standard		IEC 61131-9	
Transmission type		COM3 (230,4 kBaud)	
IO-Link revision		1.1	
SIO mode		no	
Required master port class		A	
Min. process cycle time	[ms]	4	
Supported DeviceIDs	Type of operation	DeviceID	
	Acyclic parametrisation	1316	
	Factory setting: parametrisation via Pdout	1315	
Note	Parameterization can be changed from cyclical to acyclical.		
	For further information please see the IODD PDF file at "Downloads"		
Operating conditions			
Ambient temperature	[°C]	-25...60	
Storage temperature	[°C]	-25...70	
Max. relative air humidity	[%]	90	
Max. height above sea level	[m]	2000	
Protection		IP 65; IP 67	
Protection rating (NEMA 250)		6P	
Degree of soiling		2	
Chemical media	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA	
	NEMA 250 5.13.1	AA	

AL2605



IO-Link input/output module

IOL MOD PL 8XMP/DX E M12 IP67

Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
MTTF	[years]	35

Mechanical data		
Weight	[g]	394
Dimensions	[mm]	26 x 59.3 x 208
Material	housing: PA orange; Socket: brass nickel-plated	
Sealing material	FKM	
Tightening torque	[Nm]	< 0.8

Displays / operating elements		
Display	Power	1 x LED, green
	fault	1 x LED, red
	Function	1 x LED, yellow

Accessories	
Accessories (optional)	protective cap for M12 sockets

Remarks	
Pack quantity	1 pcs.

Electrical connection - AUX

Connector: 1 x M12; coding: L



X31		
1	+ 24 V DC (U _{Ai})	
2	GND (U _A /U _{Ai})	
3	not used	
4	+ 24 V DC (U _A)	
5	functional earth	

AL2605



IO-Link input/output module

IOL MOD PL 8XMP/DX E M12 IP67

Electrical connection - IO-Link

Connector: 1 x M12; coding: A




X1

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	IO-Link

Electrical connection - inputs / outputs

Connector: 8 x M12; coding: A; sealing: FKM



X1.0...X1.7

1	Sensor supply + 24 V DC (UA/UAi)
2	multifunctional input I2 Digital output O2
3	Sensor supply GND (UA/UAi)
4	digital input/output I/O1
5	not used