


# ANT600



## RFID read/write head HF

DTRHF HLRWIDUS03



- 1 LED operating status
- 2 LED display
- 3 Mounting thread: M4 max. insertion depth: 15 mm



### Application

Application	Detection of objects on transport equipment
Radio approval for	EU/RED; Japan; Australia; China; Taiwan; India; Singapore; Ukraine; Malaysia; Brazil; Canada; Mexico; New Zealand; South Korea; USA; Vietnam
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".

### Electrical data

Operating voltage [V]	19.2...28.8 DC; (supply only via the DTE10x evaluation unit)
Current consumption [mA]	< 150
Protection class	III
Operating frequency [MHz]	13,56

### Monitoring range

Distance write/read head front [mm]	400
Distance write/read head side [mm]	600
Distance to the ID tag [mm]	referred to the ID tag E80384 : < 190
	referred to an ISO card E80407 : < 230

### Interfaces

Communication interface	DATA / DTE10x
-------------------------	---------------

### Operating conditions

Ambient temperature [°C]	-20...60
Storage temperature [°C]	-25...80
Protection	IP 67

### Tests / approvals

Shock resistance	EN 60068-2-27	40 g 6 ms / bump
	EN 60068-2-27	50 g 11 ms / single shock
Vibration resistance	EN 60068-2-6	2 g 10...150 Hz

ANT600



RFID read/write head HF

DTRHF HLRWIDUS03

UL approval	Ta	-20...60 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E205959

Mechanical data		
Weight	[g]	450
Dimensions	[mm]	120 x 50 x 113
Material		PBT; PC; stainless steel

Displays / operating elements		
Display	Power	1 x LED, green
	tag communication	4 x LED display, yellow signal strength ID tag

Remarks		
Remarks	For the distances to other ID tags see the respective data sheet (E803xx)	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A



Connection

