



Article no longer available - archive entry

# No scale drawing available



## Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

## Application

Application	universal evaluation of pulse sequences with regard to overspeed and underspeed; Rotational speed monitoring
-------------	--

## Electrical data

Nominal voltage AC	[V]	< 230
Nominal voltage DC	[V]	24
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	50...60
Auxiliary energy for sensors DC	[V]	24; ( $\leq 30$ mA)

## Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1; Number of relay outputs: 1
------------------------------	---

## Outputs

Number of relay outputs	1
Contact rating	8 A / 1250 VA / 250 V AC
Number of analog outputs	1
Analog current output	[mA] 0...20
Max. load	[ $\Omega$ ] 500

## Measuring/setting range

Setting range	[Imp/min] 50...500
---------------	--------------------



## Evaluation unit for speed monitoring

D100/230VAC/0-20mA

Accuracy / deviations		
Hysteresis	[% of Sr]	5...100
Repeatability	[% of Sr]	1
Reaction times		
Start-up delay	[s]	0.5...15
Software / programming		
Adjustment of the switch point	fine adjustment within the range with potentiometer	
Operating conditions		
Ambient temperature	[°C]	0...70
Protection	IP 40	
Protection rating terminals	IP 20	
Mechanical data		
Housing	housing for DIN rail mounting	
Material	plastics	
Displays / operating elements		
Display	Switching status	LED, red
Electrical connection		
Connection		