



## Evaluation unit for speed monitoring

D100/230VAC/EXT.POT.

Article no longer available - archive entry

# No scale drawing available

## Product characteristics

Housing	housing for DIN rail mounting
---------	-------------------------------

## Application

Application	universal evaluation of pulse sequences with regard to overspeed and underspeed; Rotational speed monitoring
-------------	--

## Electrical data

Nominal voltage AC	[V]	< 230
Nominal voltage DC	[V]	24
Nominal voltage tolerance	[%]	10
Nominal voltage tolerance 2	[%]	10
Nominal frequency AC	[Hz]	50...60
Auxiliary energy for sensors DC	[V]	24; ( $\leq 30$ mA)

## Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 1
------------------------------	----------------------------

## Outputs

Number of relay outputs	1
Contact rating	8 A / 1250 VA / 250 V AC

## Measuring/setting range

Setting range	[Imp/min]	5...5000
---------------	-----------	----------

## Accuracy / deviations

Hysteresis	[% of Sr]	5...100
Repeatability	[% of Sr]	< 5

## Reaction times

Start-up delay	[s]	0.5...15
----------------	-----	----------



## Evaluation unit for speed monitoring

D100/230VAC/EXT.POT.

Software / programming		
Adjustment of the switch point	fine adjustment within the range with potentiometer	
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing	housing for DIN rail mounting	
Material	plastics	
Displays / operating elements		
Display	Switching status	LED, red
Remarks		
Remarks	*) special design	
Electrical connection		
Connection		