


DI520A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/3D



1 potentiometer



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Dimensions [mm]	M30 x 1.5 / L = 80

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes

Monitoring range

Sensing range [mm]	10
Sensing range adjustable	no
Real sensing range S_r [mm]	$10 \pm 10\%$
Operating distance [mm]	0...8.1

Measuring/setting range

Setting range [Imp/min]	5...3600
-------------------------	----------

DI520A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/3D

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	10
Reaction times		
Start-up delay	[s]	15
Max. damping frequency	[Imp/min]	18000
Software / programming		
Adjustment of the switch point	multiturn potentiometer	
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...60
Protection	IP 65; IP 67	
Tests / approvals		
Approval	IECEx BVS 17.0094X	
ATEX marking	 II 3D Ex tc IIIC T80°C Dc X	
EMC	EN 60947-5-2	
MTTF	[years]	656
Mechanical data		
Weight	[g]	320
Mounting	flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 80
Thread designation	M30 x 1.5	
Material	brass special coating; PA; TPE-U	
Displays / operating elements		
Display	Switching status	1 x LED, green
	input signal	1 x LED, yellow
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Remarks	Recommendation Check the safe functioning of the unit after a short circuit.	

DI520A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/3D

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm²

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue