


Male cordsets

ASTGN040MSS0020K04



Application

System	Free from silicone; Halogen-free; gold-plated contacts; screened cable; Drag chain suitability
Design	Ethernet cable, D-coded
Application	Industrial Ethernet; CAT5/CAT5e; 100 Mbit/s; Industrial applications
Free from silicone	yes

Electrical data

Operating voltage [V]	30 AC / 60 DC
Protection class	III
Max. current load total [A]	4

Operating conditions

Ambient temperature [°C]	-25...90
Ambient temperature (moving) [°C]	-25...90
Protection	IP 65; IP 67

Mechanical data

Weight	[g]	1246.7	
Molded-body material		TPU (urethane)	
Material nut		brass, nickel-plated	
Drag chain suitability		yes	
Drag chain suitability		Bending radius for flexible applications	min. 10 x cable diameter
		Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
		Bending cycles	> 3 Mio.
		Torsional strain	± 180 °/m

EVC896



Male cordsets


ASTGN040MSS0020K04

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug


Connector: 1 x M12, straight; coding: D; Moulded body: TPU (urethane), black; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.2 Nm; Shielded connection cable: shield connected



Electrical connection

Cable: 20 m, PUR, Halogen-free, green, Ø 6.5 mm, screened; PROFINET Type C; 4 x 0.34 mm² (7 x Ø 0.25 mm)

Connection



BU =	Core colors :
OG =	blue
WH =	orange
YE =	white
	yellow