


DI524A



Compact evaluation unit for speed monitoring

DIA3010-WRKG/IO/US/3D



1 potentiometer



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / closed; (configurable)
Sensing range	[mm]	10
Communication interface		IO-Link
Dimensions	[mm]	M30 x 1.5 / L = 92.3
Application		
Application		simple evaluation of rotating and linear movement with regard to underspeed; blocking
Electrical data		
Nominal voltage DC	[V]	10...36
Current consumption	[mA]	< 22
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-time current rating of switching output	[mA]	250
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	10
Sensing range adjustable		no
Operating distance	[mm]	0...8.1
Measuring/setting range		
Setting range	[Imp/min]	5...3600

DI524A



Compact evaluation unit for speed monitoring

DIA3010-WRKG/IO/US/3D

Measuring principle	inductive		
Accuracy / deviations			
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3		
Hysteresis [% of Sr]	10		
Reaction times			
Start-up delay [s]	0...30		
Max. damping frequency [Imp/min]	18000		
Software / programming			
Adjustment of the switch point	Multiturn potentiometer or IO-Link		
Interfaces			
Communication interface	IO-Link		
Operating conditions			
Ambient temperature [°C]	-25...60		
Storage temperature [°C]	-25...60		
Protection	IP 65; IP 67		
Tests / approvals			
Approval	IECEx BVS 17.0094X		
ATEX marking	 II 3D Ex tc IIIC T80°C Dc X		
EMC	EN 60947-5-2		
Shock resistance	DIN EN 60947-5-2		
Vibration resistance	DIN EN 60947-5-2		
MTTF [years]	656		
Mechanical data			
Weight [g]	268		
Mounting	flush mountable		
Dimensions [mm]	M30 x 1.5 / L = 92.3		
Thread designation	M30 x 1.5		
Material	brass special coating; PA; stainless steel; TPE-U		
Displays / operating elements			
Display	Switching status	1 x LED, green	
	input signal	1 x LED, yellow	
Accessories			
Items supplied	lock nuts: 2		
Electrical connection			

Connector: 1 x M12; coding: A





DI524A



Compact evaluation unit for speed monitoring

DIA3010-WRKG/IO/US/3D

Connection



4: OUT / IO-Link