


EVC939



Female cordset


ADOGH050MSD0002C05



Application		
Special feature	Halogen-free; gold-plated contacts; screened cable; Drag chain suitability	
Application	CAN bus; for mobile applications	
Electrical data		
Operating voltage [V]	< 30 AC / < 36 DC	
Max. current load total [A]	4	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 67; IP 68; IP 69K	
Mechanical data		
Weight [g]	214.5	
Dimensions [mm]	14.5 x 14.5 x 43.9	
Molded-body material	TPU (urethane)	
Material nut	brass, nickel-plated	
Sealing material	FKM	
Drag chain suitability	yes	
Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²
	Bending cycles	> 5 Mio.
	Torsional strain	± 180 °/m
Remarks		
Pack quantity	1 pcs.	

Electrical connection	
Cable: 2 m, PUR, Halogen-free, lilac, Ø 8.4 mm, screened; RD / BK: 2 x 0.75 mm ² (42 x Ø 0.15 mm) + WH / BU: 2 x 0.5 mm ² (19 x Ø 0.19 mm) + screen: 1 x 0.75 mm ² (42 x Ø 0.15 mm)	

Electrical connection - Socket	
Connector: 1 x M12, straight; coding: A; Contacts: 5, gold-plated; Moulded body: TPU (urethane), black; Locking: brass, nickel-plated; sealing: FKM; Tightening torque: 0.6...1.5 Nm	




EVC939



Female cordset

ADOGH050MSD0002C05

Connection



Core colors :
BK = black
BU = blue
RD = red
WH = white
screen = screen