


DTI434



RFID read/write head HF

DTRHF IBRWIOUS03



Application

Application	Detection of objects on transport equipment
Radio approval for	USA; Canada; EU/RED; Australia; China; Singapore; Japan; Taiwan; India
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".

Electrical data

Operating voltage	[V]	19.2...28.8 DC
Current consumption	[mA]	< 50
Protection class		III
Operating frequency	[MHz]	13,56
RFID standard		ISO 15693

Monitoring range

Distance to the ID tag	[mm]	referred to 30 mm coin tag; I- CODE SLI	: ≤ 30
------------------------	------	--	-----------

Interfaces

Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
Profiles	Smart Sensor: Device Identification				
SIO mode	no				
Required master port class	A				
Supported DeviceIDs	<table><tr><th>Type of operation</th><th>DeviceID</th></tr><tr><td>default</td><td>967</td></tr></table>	Type of operation	DeviceID	default	967
Type of operation	DeviceID				
default	967				

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 67; IP 69K

DTI434



RFID read/write head HF

DTRHF IBRWIOUS03

Tests / approvals		
Shock resistance	EN 60068-2-27	40 g 6 ms / repetitive
	EN 60068-2-27	50 g 11 ms / not repetitive
Vibration resistance	EN 60068-2-6	20 g 10...2000 Hz
Electrical safety	EN 61010-2-201 : 2013 +AC:2013	

Mechanical data	
Weight [g]	197.5
Housing	tubular
Mounting	flush mountable
Dimensions [mm]	M30 x 1.5 / L = 70
Thread designation	M30 x 1.5
Material	housing: stainless steel (1.4301 / 304); Protective cover: PPS


Displays / operating elements		
Display	Power	1 x LED, green
	tag communication	1 x LED, yellow

Accessories	
Items supplied	Nut 2 x M30 x 1,5

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

