




Inductive sensor

Elektronikteil/IM0007

Article no longer available - archive entry

Alternative articles: E10168
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Output function		normally open / closed; (selectable)
Sensing range	[mm]	15
Housing		rectangular
Electrical data		
Operating voltage	[V]	20...250 AC/DC
Reverse polarity protection		no
Outputs		
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	6
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100

E10117



Inductive sensor

Elektronikteil/IM0007

Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Switching frequency DC	[Hz]	55
Short-circuit protection		no
Overload protection		no

Monitoring range

Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Mounting		flush mountable
Material		PPE

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Remarks		5 positions of the active zone possible
Pack quantity		1 pcs.

Electrical connection

Mounting base: ...2.5 mm²

Connection

