


E10219



Female cordset

ADOAG032--S0005A03

Article no longer available - archive entry



Application		
System	Halogen-free	
Electrical data		
Operating voltage	[V]	10...30 DC
Outputs		
Electrical design	PNP	
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection	IP 65	
Mechanical data		
Weight	[g]	146.6
Material	TPU (urethane) transparent	
Molded-body material	TPU (urethane), transparent	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
Remarks		
Pack quantity	1 pcs.	

E10219



Female cordset

ADOAG032--S0005A03

Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 4.5 mm; 3 x 0.25 mm² (42 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU (urethane), transparent; Locking: Snap-in



Connection



BK = Core colors :
BN = black
BU = brown
BU = blue