


E11627



T-splitter

T SPLITTER M12/2XUS



Application	
Application	Industrial applications
Electrical data	
Operating voltage [M]	< 30 AC / < 36 DC
Max. current load per module/slot [A]	3
Max. current load total [A]	3
Operating conditions	
Ambient temperature [°C]	-25...90
Protection	IP 68
Mechanical data	
Weight [g]	39.7
Material	housing: PUR
Material nut	brass, nickel-plated
Accessories	
Items supplied	Protective caps: 1
Remarks	
Pack quantity	1 pcs.

E11627



T-splitter


T SPLITTER M12/2XUS

Electrical connection

Connection


AN_i_0925_GG

Original Scale Drawing (MTD)



↓ 32% ↑ 312,5%

EPS Source
Product Scale Drawing
Frame Size: 75 mm x 45 mm



Connector: 1 x M12; Locking: brass, nickel-plated