


E11022



Wiring block

ZDO8H05HMSS0010H19

Article no longer available - archive entry



Application

System	Free from silicone; Halogen-free; gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	10...30 DC
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12

Outputs

Electrical design	PNP
-------------------	-----

Operating conditions


Ambient temperature	[°C]	-15...80
Protection		IP 67

E11022



Wiring block

ZDO8H05HMSS0010H19

Mechanical data		
Material	TPU (urethane)	
Molded-body material	TPU (urethane)	
Number of ports splitter box	8	
Connector type	M12	
Displays / operating elements		
Display	Switching status	16 x LED, yellow
	Power	1 x LED, green
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 10 m, PUR, Halogen-free; 16 x 0.5 mm ² (63 x Ø 0.1 mm) + 3 x 1.0 mm ² (127 x Ø 0.1 mm)		
Electrical connection - slot		
Connector: 8 x M12; coding: A; Moulded body: TPU (urethane); Contacts: gold-plated; Tightening torque: 0.5 Nm		
		

E11022



Wiring block

ZDO8H05HMSS0010H19

Connection



Core colors :

BK =	black
BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
RD =	red
VT =	lilac
WH =	white
YE =	yellow

E11022

Wiring block

ZDO8H05HMSS0010H19

