


EVC119



Connection cable

VDOGH040MSS00,7H04STAH040MSS

Please see the technical note under "Downloads"



| Application | |
|---|--|
| System | Free from silicone; Halogen-free; gold-plated contacts; Drag chain suitability |
| Free from silicone | yes |
| Electrical data | |
| Operating voltage [V] | < 250 AC / < 300 DC |
| Protection class | II |
| Max. current load total [A] | 4 |
| Operating conditions | |
| Ambient temperature [°C] | -25...90 |
| Note on ambient temperature | cULus: ...75 |
| Ambient temperature (moving) [°C] | -25...90 |
| Note on ambient temperature (moving) | cULus: ...75 |
| Storage temperature [°C] | -25...55 |
| Storage humidity [%] | 10...100 |
| Other climatic conditions for storage according to stated class | 1K22/ DIN 60721-3-1 |
| Protection | IP 65; IP 67; IP 68; IP 69K |
| Mechanical data | |
| Weight [g] | 59.2 |
| Dimensions [mm] | 30.5 x 15.5 x 36.5 |



Connection cable

VDOGH040MSS00,7H04STAH040MSS


| | | |
|------------------------|--|--|
| Material | housing: TPU (urethane) orange; sealing: FKM | |
| Material nut | brass, nickel-plated | |
| Drag chain suitability | yes | |
| Drag chain suitability | Bending radius for flexible applications | min. 10 x cable diameter |
| | Travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² |
| | Bending cycles | > 5 Mio. |
| | Torsional strain | ± 180 °/m |

Remarks

| | |
|---------------|---|
| Notes | Please see the technical note under "Downloads" |
| Pack quantity | 1 pcs. |

Electrical connection - plug


Connector: 1 x M12, angled; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Electrical connection


Cable: 0.7 m, PUR, Halogen-free, black, Ø 4.3 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm






Connection cable

VDOGH040MSS00,7H04STAH040MSS

Diagrams and graphs

Characteristic curve for derating



Derating $I_{max} \cdot 0.8$ (DIN EN 60512-5-2)

X Ambient temperature [°C]

Y Current [A]