


E12167



Female cordset

ADOGH080MSS0010B08

For 8-wire cordsets the core colors are not standardized.
Please note the wiring of the sensor and the cordsets (see data sheet).



Application	
Application	Industrial applications
Electrical data	
Operating voltage [V]	< 30 AC / < 36 DC
Max. current load total [A]	2
Operating conditions	
Ambient temperature [°C]	-40...80
Protection	IP 67
Mechanical data	
Weight [g]	537.5
Dimensions [mm]	15 x 15 x 43
Molded-body material	TPU (urethane)
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 10 m, PUR, black, Ø 6.6 mm; 8 x 0.25 mm ² (14 x Ø 0.15 mm)	
Electrical connection - Socket	
Connector: 1 x M12, straight; coding: A; Contacts: 8; Moulded body: TPU (urethane), black; Locking: brass, nickel-plated; Tightening torque: 1...1.5 Nm	


E12167



Female cordset

ADOGH080MSS0010B08

Connection



Colors to DIN 47100
Core colors :

BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
RD =	red
WH =	white
YE =	yellow