


E12318



Male cordsets

ASTGH020MSS0002C02



Application

System	Halogen-free; gold-plated contacts; screened cable; Drag chain suitability
--------	--

Electrical data

Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4; (...40 °C)

Operating conditions

Ambient temperature	[°C]	-40...70
Ambient temperature (moving)	[°C]	-20...50
Protection		IP 67

Mechanical data

Weight	[g]	145.2
Dimensions	[mm]	14.5 x 14.5 x 48.5
Material		PUR
Molded-body material		PUR
Material nut		brass, nickel-plated
Drag chain suitability		yes
Drag chain suitability	Bending radius for flexible applications	min. 7.5 x cable diameter
	Bending radius for fixed installation	min. 10 x cable diameter
	Travel speed	max. 5.5 m/s for a horizontal travel length of 5m and max. acceleration of 10 m/s²
	Bending cycles	> 5 Mio.
	max. permissible tensile strength	50 N/mm² static
		20 N/mm² dynamic

E12318



Male cordsets

ASTGH020MSS0002C02

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR, Halogen-free, lilac, Ø 8 mm, screened; 2 x 0.25 mm²

Electrical connection - plug

Connector: 1 x M12, straight; coding: B; Moulded body: PUR; Locking: knurled nut, brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6 Nm; Shielded connection cable: shield connected



Connection

