


E20609



Fiber optic through beam sensor

FE-11-EPA-M3/F1X0,5/2M



Application

Function principle	Through-beam sensor
Application	Small bending radius

Monitoring range

Range with fiber optic amplifier type	OB50; OBF; OCF; OO50
---------------------------------------	----------------------

OB50

Range of fiber optics [mm]	60
----------------------------	----

OBF

Range of fiber optics [mm]	130
----------------------------	-----

OCF (High Power)

Range of fiber optics [mm]	2080
----------------------------	------

OO50

Range of fiber optics [mm]	160
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-40...70
--------------------------	----------

Mechanical data

Weight [g]	34
Version of sensing head	straight
Sensing head thread	M3
Sensing head length [mm]	14.5
Total length [mm]	2000
Min. bending radius [mm]	10
Fiber arrangement	●
Core diameter [mm]	0.5
Fiber material	PMMA
Fiber head material	aluminum
Fiber sheath material	PE

Accessories

Items supplied	Hexagon nuts: 4 x M3 tooth lock washers: 4 Adapter: 1 x OBF Adapter: 1 x OCF Adapter: 1 x OOF
Accessories (optional)	Cutter for fibers:, E20600

Remarks

Pack quantity	1 pcs.
---------------	--------