

E20768




Sensing head for fiber optic through-beam sensor

FE-11-EPA-M5x30/F1x0,5

Article no longer available - archive entry

Alternative articles: E20767
When selecting an alternative article and accessories please note that technical data may differ!




Application		
Function principle		Through-beam sensor
Monitoring range		
Range with fiber optic amplifier type		OB50; OBF; OO50
OB50		
Range of fiber optics	[mm]	45
OBF		
Range of fiber optics	[mm]	80
OO50		
Range of fiber optics	[mm]	120
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	0.011
Version of sensing head		straight

E20768



Sensing head for fiber optic through-beam sensor

FE-11-EPA-M5x30/F1x0,5

Sensing head thread	M5
Total length [mm]	configurable
Fiber arrangement	
Material	housing: brass white bronze coated
Fiber material	PMMA
Fiber head material	aluminum
Accessories	
Items supplied	Hexagon nuts: 4 x M5
	washers: 4
Remarks	
Pack quantity	1 pcs.