




Fiber optic through beam sensor

FE-50-V-V-M5/16/2M

Article no longer available - archive entry



Application

Function principle	Through-beam sensor
--------------------	---------------------

Monitoring range

Range with fiber optic amplifier type	ODF; OMF
---------------------------------------	----------

ODF

Range of fiber optics [mm]	4
----------------------------	---

OMF

Range of fiber optics [mm]	1000
----------------------------	------

Operating conditions

Ambient temperature [°C]	-58...315
--------------------------	-----------

Mechanical data

Version of sensing head	straight
Total length [mm]	2000
Min. bending radius [mm]	19
Fiber material	glass
Fiber head material	stainless steel (1.4305 / 303)
Fiber sheath material	stainless steel (1.4305 / 303)

E20977



Fiber optic through beam sensor

FE-50-V-V-M5/16/2M

Remarks	
Pack quantity	1 pcs.