




Fiber optic diffuse reflection sensor

FT-18-P-A-R5

Article to be discontinued



Application		
Function principle		Diffuse reflection sensor
Application		For use in industrial environments
Monitoring range		
Range with fiber optic amplifier type		OGF
OGF		
Range fiber optics	[mm]	12
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Weight	[g]	59.4
Version of sensing head		angled
Sensing head diameter	[mm]	5
Sensing head length	[mm]	10
Total length	[mm]	600
Min. bending radius	[mm]	20
Fiber arrangement		Ⓜ
Material		Adapter: PPE

E20384



Fiber optic diffuse reflection sensor

FT-18-P-A-R5

Fiber material	glass
Fiber head material	aluminum
Fiber sheath material	PVC
Accessories	
Items supplied	Mounting clamp:, E10221
Remarks	
Pack quantity	1 pcs.