




Welding thermowell for temperature sensors

THERMOWELL, D6/WELD-IN/L=230



EC 1935/2004 EHEDG Certified



Application		
Design		for temperature sensors EL = 300 mm
Pressure rating	[bar]	400
Accuracy / deviations		
Max. permissible flow velocity	[m/s]	25
Mechanical data		
Weight	[g]	1236
Material		stainless steel (1.4404 / 316L)
Sensor connection		1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT
Process connection		Welding adapter Ø 38,1 mm
Installation length EL	[mm]	191
Bore length BL	[mm]	228.6
Remarks		
Pack quantity		1 pcs.