


E43310



Welding adapter for process sensors

ADAPT G1/2-WELD FOR PIPE 3A



1 Leakage port



EC 1935/2004 EHEDG Certified FCM FDA

Application

Design	for pipes, with leakage port (3A)	
Pressure rating	50 bar	5 MPa
Note on pressure rating	for the connection sensor - adapter	

Tests / approvals

Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	

Mechanical data

Weight	[g]	160
Materials (wetted parts)	stainless steel (1.4435 / 316L)	
Sensor connection	G 1/2 sealing cone	
Process connection	Welding adapter DN25 (29 x 1,5); Maße gemäß DIN 11866; Reihe A DIN	
Surface characteristics Ra/Rz of the wetted parts	Ra < 0.4 µm / Rz = 4 µm	

Accessories

Items supplied	O-rings:, FKM
----------------	---------------

Remarks

Pack quantity	1 pcs.
---------------	--------