


# EVF383



## Female cordset

ADOGH040VAS0010S04



| Application   |  |  |
|---|--|--|
| Special feature   | Free from silicone; Halogen-free; gold-plated contacts; screened cable; Drag chain suitability |  |
| Application   | sanitary and wet areas in the food industry  |  |
| Free from silicone  | yes  |  |
| Electrical data   |  |  |
| Operating voltage [V]   | < 50 AC / < 60 DC  |  |
| Protection class  | III  |  |
| Max. current load total [A]                                     | 4  |  |
| Operating conditions  |  |  |
| Ambient temperature [°C]  | -25...100  |  |
| Ambient temperature (moving) [°C]                               | 0...100  |  |
| Storage temperature [°C]  | -25...55   |  |
| Storage humidity [%]  | 10...100   |  |
| Other climatic conditions for storage according to stated class | 1K22/ DIN 60721-3-1  |  |
| Protection  | IP 65; IP 67; IP 68; IP 69K  |  |
| Mechanical data   |  |  |
| Weight [g]  | 916.35   |  |
| Dimensions [mm]   | 15.5 x 15.5 x 47   |  |
| Molded-body material  | PP, Halogen-free   |  |
| Material nut  | stainless steel (1.4404 / 316L)  |  |
| Sealing material  | EPDM   |  |
| Drag chain suitability  | yes  |  |
| Drag chain suitability  | Bending radius for flexible applications   | min. 10 x cable diameter   |
|   | Travel speed   | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup> |
|   | Bending cycles   | > 1 Mio.   |
|   | Torsional strain   | ± 180 °/m  |
| Remarks   |  |  |
| Pack quantity   | 1 pcs.   |  |

# EVF383



## Female cordset

ADOGH040VAS0010S04

### Electrical connection


Cable: 10 m, MPPE, Halogen-free, grey, Ø 5.2 mm, screened; 4 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: PP, Halogen-free; Locking: stainless steel (1.4404 / 316L); sealing: EPDM; Tightening torque: 0.6...1.5 Nm; Shielded connection cable: shield not connected



### Connection



Core colors :  
BK = black  
BN = brown  
BU = blue  
WH = white