


Female cordset

ADOGH046VAS0005E04



Application

System	Free from silicone; gold-plated contacts; Drag chain suitability
Application	sanitary and wet areas in the food industry
Free from silicone	yes

Electrical data

Operating voltage	[V]	10...36 DC
Protection class		II
Max. current load total	[A]	4

Outputs

Electrical design	PNP
-------------------	-----

Operating conditions

Ambient temperature	[°C]	-25...100
Note on ambient temperature		cULus: ...50
Ambient temperature (moving)	[°C]	5...100
Note on ambient temperature (moving)		cULus: ...50
Protection		IP 65; IP 67; IP 68; IP 69K

Mechanical data

Weight	[g]	205.5
Dimensions	[mm]	15.5 x 15.5 x 45
Material		housing: PVC black transparent; sealing: EPDM
Material nut		stainless steel (1.4404 / 316L)
Drag chain suitability		yes

EVT462



Female cordset

ADOGH046VAS0005E04

Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
	Bending cycles	> 1 Mio.
	Torsional strain	± 180 °/m

Displays / operating elements

Display	Switching status	4 x LED, yellow
	Power	2 x LED, green

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection


Cable: 5 m, PVC, orange, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Connection



BK = black
BN = brown
BU = blue
WH = white

Core colors :