


# EVC538



## Female cordset

ADOGH040MSS0002K04



### Application

System	Free from silicone; Halogen-free; gold-plated contacts; screened cable; Drag chain suitability
Free from silicone	yes

### Electrical data

Operating voltage	[V]	< 50 AC / < 60 DC
Protection class		III
Max. current load total	[A]	4

### Operating conditions

Ambient temperature	[°C]	-25...90
Note on ambient temperature		cULus: ...75 °C
Ambient temperature (moving)	[°C]	-25...90
Note on ambient temperature (moving)		cULus: ...75 °C
Protection		IP 65; IP 67

### Mechanical data

Weight	[g]	99.4
Dimensions	[mm]	15.5 x 15.5 x 45
Material		housing: TPU (urethane) orange; sealing: FKM
Material nut		brass, nickel-plated
Drag chain suitability		yes

# EVC538



## Female cordset

ADOGH040MSS0002K04

Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>
	Bending cycles	≥ 2 Mio.
	Torsional strain	± 180 °/m

### Remarks


Pack quantity	1 pcs.
---------------	--------

### Electrical connection


Cable: 2 m, PUR, Halogen-free, black, Ø 4.9 mm, screened; 4 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm;  
Shielded connection cable: shield connected



### Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white




Female cordset


ADOGH040MSS0002K04

Diagrams and graphs

Shielding characteristics



x Frequency (MHz)  
y Shielding characteristics (dB)  
according to DIN EN 60512-23-3



Derating  $I_{max} \cdot 0.8$  DIN EN 60512-5-2  
X Ambient temperature [°C]  
Y Current [A]