




Inductive area sensor

SIT-3070-BPKG 15m KABEL

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	20...70
Housing		tubular
Dimensions	[mm]	Ø 100 / L = 45
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open



Inductive area sensor

SIT-3070-BPKG 15m KABEL

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	5
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	20...70
Sensing range adjustable		yes
Factory setting sensing range	[mm]	70
Real sensing range Sr	[mm]	70 ± 10 %
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	< 15
Switch-point drift	[% of Sr]	-15...15
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight	[g]	0.001
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 100 / L = 45
Material		PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

I17006



Inductive area sensor

SIT-3070-BPKG 15m KABEL

Electrical connection

Cable: 15 m, PVC; 3 x 0.5 mm²

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue